

## www.choicebyglastender.com



To view cleaning and care instructions, please visit: https://www.glastender.com/PDF/F-423-011\_ss\_clean\_care.pdf

Project:		AIA#
Item #:	Qty:	SIS#
Model #:		515.1

# Soda Gun Holders

Patented. For more information visit: https://www.glastender.com/patents

C-SHA-4, C-SHA-4-ED, C-SHA-6, C-SHA-6-ED, C-SHB-4, C-SHB-4-ED, C-SHB-6, C-SHB-6-ED, C-SHP-4, C-SHP-4-ED, C-SHP-6, C-SHP-6-ED

### Standard Features

- All stainless steel construction
- Designed to house the manifold of Wunder-Bar® or Schroeder America<sup>TM</sup> 8 to 14 button soda guns
- Includes integral drip pan with radius corners for easy cleaning
- Built-in holder for soda gun
- Top cover is removable for access to the soda manifold
- Allows you to dictate the soda gun location
- Eliminates the need for tubing bundles above the work surface
- Designed to mount to at least one other piece of underbar equipment (there is no provision for leg mounting)
- Pre-aligned mounting holes and bolts ensure a secure and exact fit when mounting adjoining units
- Extra deep "-ED" models available to align with extra-deep style ice bins

# Specifications

Drain

• 1/2" welded tailpiece

Materials

All stainless steel construction

#### Installation Details





Figure 3







Figure 1 Figure 2

- 1. Remove three cover screws and the cover (Figure 1).
- 2. Remove the manifold containment bracket by removing the thumbscrew (Figure 2).
- 3. Plumb drip pan drain, which may be more convenient to do while the cover is removed.
- 4. Connect soda tubing from inside housing to soda gun manifold (Figure 3).

Figure 4

Figure 5

- 5. Insert manifold and lines into the housing while placing the soda gun line in the front cut-out. Secure the manifold in place with the bracket and thumbscrew removed in step two (Figure 4).
- 6. Reattach cover with the three screws removed in step one (Figure 5).
- 7. Set the soda gun in the holder (Figure 6).
- 8. Installation complete.

Glastender, Inc. • 5400 North Michigan Road • Saginaw, MI • 48604-9780 989.752.4275 • 800.748.0423 • Fax 989.752.4444 www.glastender.com

Approval/Notes:

Specifications subject to change without notice. For current specifications please visit our website.

## **Dimensional Information**





